

Dual-Action Shaker KL 2



Description

Depending on the task the shaking motion of the Dual Action Shaker KL 2 can be switched from orbital to reciprocating.

Basic Equipment

Basic device incl. rack system with 3 clamping strips and rubber mat

Loading Capacity

Erlenmeyer flasks 250 ml 9 pieces

Separating funnels 250 ml 1 pieces

You will find further loading possibilities [here](#)

Details

Motion:	can be switched from orbital to reciprocating (horizontal)
Shaking platform:	300 x 300 mm
Max. load:	2 kg
Shaking speed:	30 - 420 rpm, steplessly adjustable
Stroke:	8 mm
Timer:	0 - 120 min / continuous
Order No.:	6115 000
Accessory:	Spannleiste v 0050 477 Spannleiste h 0050 118 Klammerleiste 0050 206 Federleiste 0050 207 Reagenzglasgestell mit 44 Bohrungen à 14 mm Ø Reagenzglasgestell mit 44 Bohrungen à 16 mm Ø Reagenzglasgestell mit 44 Bohrungen à 18 mm Ø Reagenzglasgestell mit 14 Bohrungen à 30 mm Ø

Technical specifications

Electrical supply:	230 V or 115 V, 50 / 60 Hz please indicate in case of order
Enclosure protection:	IP 21
Heat emission:	approx. 4 W
Ambient temperature:	5°C bis 50°C
Relative humidity:	~ 85 %
Dimensions (w x d x h):	355 x 455 x 195 mm
Weight:	13,5 kg